


Drive

11.10.16 12:31:24

1146 20161006

Time diagram



No. 1.1 _____

No. 1.2 _____

No. 1.3 _____

No. 1.4 _____

No. 1.5 _____

No. 1.6 _____

No. 1.7 _____

T1: 12291.170 ms

T2: 29186.886 ms

dT: 16895.717 ms

Y(T1):	471.785 V _{rms}
--------	--------------------------

Y(T2): 445.167 Vrms

dY: -26.618 V_{rms}

No.	Signal	Unit	Y min	Y max
1	Measurement (23) 07.10.16 06:33:52			
1.1	HoiGan1.r62	rpm	-1690.428	1690.428
1.2	HoiGan1.r63[1]	rpm	-1690.428	1690.428
1.3	HoiGan1.r68[1]	Arms	5.304	346.887
1.4	HoiGan1.r70	V	708.910	730.390
1.5	HoiGan1.r72	Vrms	-45.906	531.054
1.6	HoiGan1.r80[1]	Nm	-317.811	1749.920
1.7	HoiGan1.r82[1]	kW	-208.695	257.757

				Date	10/11/2016				
				Editor					
				Checked					
State	Modification	Date	Name	Standard					
								Page	1
								Pg.	1