



back view




front view

center hole
DIN 332-DR M12




version with featherkey



6-pole plug size 1.5
for power

10-pole
signal plug



Einheit / unit: mm	Synchron-Servomotor Synchronous Servo Motor:
nicht tolerierte Ma? / not toleranced dimensions: ?	Optionen / options:
Ma? tab / scale: ohne / without	Gewicht / mass:
CAD CREATOR 2.3.2 (DVD-Version V02.03.02.00)	Bemerkung / notice:
	Druckdatum / print date: 18.11.2024