

niedetex.		常规
🕒 🍝 🕥 🛧 💽 > 控制面板 >	连接时使用:	
组织 ▼ 禁用此网络设备 诊断	Intel(R) Ethernet Connection (3) 12	如果网络支持此切能,则可以获取目动指派的 IP 设置。否则,你需要从网络系统管理员处获得适当的 IP 设置。
VMware Network Adapte		
已 启用	此连接使用下列项目(O):	
▲ 以太网	✓ 早Microsoft 网络客户端	●使用下面的 IP 地址(S):
网络 Intel(R) Ethernet Connecti	☑ 〒VMware Bridge Protocol ☑ 〒Microsoft 网络的文件和打印机共享	IP 地址(I): 192 . 168 . 1 . 204
	☑ 🧓 QoS 数据包计划程序	子网掩码(U): 255.255.255.0
	☑ _ Internet 协议版本 4 (TCP/IPv4)	默认网关(D): 192.168.1.1
	□ _ Microsott 网络造配器多路包装器机	
	✓ Microsoft LLDP 协议驱动程序	○ 自动获得 DNS 服务器地址(B)
	<	● 使用下面的 DNS 服务器地址(E):
	安装(N) 卸载(U)	首选 DNS 服务器(P): 8 . 8 . 8 . 8
	描述	各田 DNS 肥友哭(A)
	传输控制协议/Internet 协议。该协议是要 于在不同的相互连接的网络上通信	
		□退出时验证设置(L) 高级00
511项目 选中111项目		[12].05(¥)
5	高级 TCP/IP 设置	× e1
ব	IP 设置 DNS WINS	2,5
	IP 地址(R)	br
34		之际按照 维
	192.168.1.204	255.255.255.0
	100.10.10.3	255.255.255.0
1		conver ID 目网段任音方
1		SELVELTF_1可MF文1工态で有 編辑(E) 删除(V)
	默认网关(F):	
	网关	跃点数
	192.168.1.1	自动
	100.10.10.1	自动
	与server网关————————————————————————————————————	
	添加(D)	编辑(T) 删除(M)
	☑ 自动跃点(U)	-
	接口跃点数(N):	
Ŷ		
		1 确定 取消
L		
🗔 命令提示符 Wienagaft Windowg [版本 10 0 10	640 1]	—
(c) 2020 Microsoft Corporation.	640.1」 保留所有权利。	
C:\Users\1tn1@ping 100.10.10.2		
正在 Ping 100 10 10 2 目有 22 3	PING — pserver 地址	
来自 100.10.10.2 的回复: 字节=3	2 时间<1ms TTL=64	
来自 100.10.10.2 的回复: 字节=3	2 时间<1ms TTL=64	
来目 100.10.10.2 的回复: 子卫=3 来自 100.10.10.2 的回复: 字节=3	2 时间(Ims IIL=64 2 时间(Ims TTL=64 、————————————————————————————————————	
100 10 10 2 的 Ping 统计信息	连拍	妾止 常
数据包:已发送 = 4,已接收	= 4, 丢失 = 0 (0% 丢失),	
往返行程的估计时间(以毫秒为单位) 最短 = Oms、最长 = Oms、平t):) = Oms	
C:\Users\Itniu>		

				*
C C C C C C C C C C C C C C C C C C C	× [*			- C
	比站点不安全			
ĩ	这可能意味着,有人正在尝试欺骗你或窃取	你发送到服务器的信	E何信息。你应该立即关	闭此站点。
	乡 关闭此标签页			
	〕详细信息			
	你的电脑不信任此网站的安全证书。			
	错误代码: DLG_FLAGS_INVALID_CA			
C	¥到此网页(不推荐)			
				— П X
	om/login/	▼ 😵 证书错误 🖒	搜索	୍ତି ଛି ⇔ କ ୍
CIERCEAR Remot ×				
SIEWIENS	SINEMA Remote Con	IECT Help O	6/9/2020 3:45:25 PM 🕑	Language: English 🗸
	User name: admin			
	Password: •••••			
	Log on			
	The logon	ailed		
	PKI Log	in		
SIEMENS	SINEMA Remote Coni	iect Help@	6/9/2020 11:46:55 PM 🧿	Language: English 🗸
Logged on as "admin"	Change password			
	3			
System	i To continue, you need to change your	password.		
User accounts	* User name: Rampage]	
Security	* New password:			
 My account Change password 	Confirm password:	\$	J	
	Save			

这里点快了,跳过了一步,在上图点击 save 后的下一个页面应该是设置时间,先选择使用 PC 的时间,反正后续需要重新设置时钟同步的;选了使用 PC 的时间之后,在后续的页码上 可以看到, RC server 管理页面上的时间跟电脑一致。

下图是 server 的 interfaces,可以看出跟我们之前部署 server 虚拟机时设置的一样,后续想更改也是可以的;

							× 1
	Attps://100.10.10.2/sy	/stem/network/i	nterfaces/?next=/syster	m/network/dns/ 🔹 🔻 😵 🖬	[书错误 ひ 捜索…	(1) つう (1) (1) (1) (1) (1) (1) (1) (1) (1) (1)	3 🙂
🩆 Netv	work configuration × 📑						
S	IEMENS		SINEMA Rei	mote Connect Help	6/9/2020 3:48:	37 PM 🗿 Language: English 🔽	^
	ged on as "Rampage"		Network conf	figuration			
		3	Interfaces	DNS	Web server settings		
-	System • Overview		If you change the fo Web server is tempor	ollowing settings, existing conn rarily unreachable!	ections to devices / users can	be terminated and the	
	▶ Logfile		\checkmark	Activate the interface			
	Network configuration		Interface:				
	Date & time settings		MAC address: 0	0:0::29:da:ca:4d			
	SMS & E-mail		MAC address.	0.00.25.0a.ca.40			
	 Licenses 		MTU: 1	460			
	Update		IP address: 1	00.10.10.2			
	Upload Server		Network mask: 2	255.255.255.0			
	 Backup & restore 		Default gateway: 1	00.10.10.1			
	Debug Login			SINEMA Remote Connect	is located behind a NAT de	wice	
•	Remote connections				is located bening a new rate		
•	User accounts		WAN IP address:				
•	Security			Save			
	& My account						~
8	Ð] 18 🌽 🛥 🧕 🍖 📾 🔛 🐠 中	15:48

此处 IP 应该填入, 申请的公网 IP:

SIEMENS		SINEMA Rem	note Connect	Help 😧	6/9/2020 4:23:42 PM 🕑	Language: English 🗸
Logged on as "Rampage"		Network confi	guration			
Log off	3	Interfaces	DNS	Web serve	r settings	
 System Overview Logfile Network configuration Ping Static routes Date & time settings Date & time settings SMS & E-mail Licenses UMC settings Update Upload Server Backup & restore Syslog client Debug login Remote connections User accounts Security M yaccount 		Lif you change the foll Web server is temporal Interface: W/ MAC address: 00 MTU: 14 IP address: 10 Network mask: 25 Default gateway: 10 IV dtwork mask: 25 Default gateway: 10 IV dtwork mask: 25	owing settings, existing cor ity unreachable! Activate the interface AN 00:29.da:ca:4d 60 0.10.10.2 5.255.255.0 0.10.10.1 SINEMA Remote Connect Save	t is located beh	es / users can be terminated and	the

SIEMENS Help 🛛 Logged on a Network configuration C Interfaces DNS Web server settings ! If you change the host name, existing connections to devices / users will be terminated and the Web server will be temporarily unreachable! ▼ Svstem Overview Logfile * Host name: sinemarc.example.com Network configuration Externally resolvable host name. Date & time settings Primary DNS server: 218.2.135.1 SMS & E-mail Secondary DNS server: 61.147.37.1 Licenses Update Save Upload Server Backup & restore Debug Login Remote connections User accounts Security My account **SIEMENS** SINEMA Remote Connect Help @ 6/9/2020 3:50:45 PM () Language: English 🗸 Network configuration 3 Interfaces DNS Web server settings If you change the following settings, existing connections to devices / users can be terminated and the Web server is temporarily unreachable! ▼ System Overview I Fallback port change works only with device firmware version 4.3.1 or higher. Logfile Network configuration Port settings: Date & time settings HTTPS port: 443 SMS & E-mail Fallback port: 6220 Licenses ▶ Update Save Upload Server Backup & restore Debug Login Remote connections

User accounts Security My account

SINEMA Remote Connect

6/9/2020 4:19:22 PM (UTC +08:00) O Language: English 🗸

SIEMENS	SINEMA Remote Connect Help 6/9/2020 3:51:43 PM Language: English
Logged on as "Rampage"	Overview
 System Overview Logfile Network configuration Date & time settings SMS & E-mail Licenses Update Upload Server Backup & restore Debug Login Remote connections User accounts Security 	Software version: V1.3.0.0-01.01.00.38 License usage (activated participant / of total): 0 / 4 Configured users: 1 Configured devices: 0 Active VPN connections: 0 Users: 0 Devices: 0

SIEMENS		SINEMA Rem	ote Connect Help Ø	6/9/2020 3:53:46 PM O	Language: English 🔽	^
Logged on as "Rampage"		Update				
	3	System update	Power management			
▼ System		* Select the update file	e: E:\SINEMARC_V2.0.0.0- 浏览	ž		
 Overview 						
► Logfile			Import			
 Network configuration 						
Date & time settings						
SMS & E-mail						
 Licenses 						
Update						
Upload Server						
 Backup & restore 						
Debug Login						
Remote connections						
User accounts						
Security						
My account						V

SIEMENS		SINEMA Rem	ote Connect Help 🛛	6/9/2020 3:54:28 PM 🧿	Language: English 🔽
Logged on as "Rampage"		Update			
	3	System update	Power management		
 System Overview Logfile Network configuration Date & time settings SMS & E-mail Licenses Update Upload Server Backup & restore Debug Login Remote connections User accounts Security M account 		• Select the update file	E:\SINEMARC V2.0.0.0 浏	<u>ت</u>	
SIEMENS		SINEMA Rem	ote Connect Help @	6/9/2020 3:56:35 PM 🧿	Language: English 🔽
		Update			
	3	System update	Power management		
▼ System		 Update successfully to Select the update file 	iploaded!	ž	
Logfile					