

GNU GRUB version 2.02~beta2-36ubuntu3.9

*SINEMA RC (2.0.0.0-01.01.00.21) GNU/Linux, with Linux 4.4.0-97-generic
SINEMA RC (1.3.0.0-01.01.00.38) GNU/Linux, with Linux 4.4.0-97-generic →

Use the ↑ and ↓ keys to select which entry is highlighted.
Press enter to boot the selected OS, `e' to edit the commands
before booting or `c' for a command-line.

Welcome to SINEMA Remote Connect V2.0

System startup complete.
Please open WBM over <http://100.10.10.2>

server已成功升级到V2.0

Logged on as "Rampage"

[Log off](#)

Overview

▼ System

► Overview

- Logfile
- Network configuration
- Date & time settings
- SMS & E-mail
- Licenses
- Update
- Upload Server
- Backup & restore
- Debug Login
- Remote connections
- User accounts
- Security
- My account

Software version: V2.0.0.0-01.01.00.21

License usage (activated participant / of total): 0 / 4

Configured users: 1

Configured devices: 0

Active VPN connections: 0

Users: 0

Devices: 0

Logged on as "Rampage"

[Log off](#)

Update

System update

Power management

▼ System

► Overview

- Logfile
- Network configuration
- Date & time settings
- SMS & E-mail
- Licenses
- Update
- Upload Server
- Backup & restore
- Debug Login
- Remote connections
- User accounts
- Security
- My account

* Select the update file: E:\SINEMARC_V2.1.0.0- 浏览...

Import

Logged on as "Rampage"

[Log off](#)

▼ System

- Overview
- Logfile
- Network configuration
- Date & time settings
- SMS & E-mail
- Licenses
- Update
- Upload Server
- Backup & restore
- Debug Login
- Remote connections
- User accounts
- Security
- My account

Update

System update

Power management

* Select the update file: E:\SINEMARC_V2.1.0.0- 浏览...

Import

Logged on as "Rampage"

[Log off](#)

▼ System

- Overview
- Logfile
- Network configuration
- Date & time settings
- SMS & E-mail
- Licenses
- Update
- Upload Server
- Backup & restore
- Debug Login
- Remote connections
- User accounts
- Security
- My account

Update

System update

Power management

✓ Update successfully uploaded!

* Select the update file: 浏览...

Import

GNU GRUB version 2.02~beta2-36ubuntu3.19

SINEMA RC (2.0.0.0-01.01.00.21) GNU/Linux, with Linux 4.4.0-97-generic
SINEMA RC (2.1.0.0-01.01.00.16) GNU/Linux, with Linux 4.15.0-66-generic

Use the ↑ and ↓ keys to select which entry is highlighted.
Press enter to boot the selected OS, `e' to edit the commands
before booting or `c' for a command-line.

Welcome to SINEMA Remote Connect 02.1

System startup complete.
Please open WBM over <http://100.10.10.2>

Logged on as "Rampage"

[Log off](#)

Overview

▼ System

► Overview

- Logfile
- Network configuration
- Ping
- Static routes
- Date & time settings
- SMS & E-mail
- Licenses
- UMC settings
- Update
- Upload Server
- Backup & restore
- Syslog client
- Debug login

Order ID: 6GK1720-1AH01-0BV0

Software version: V2.1.0.0-01.01.00.16

Software downloads: <https://support.industry.siemens.com/cs/ww/de/ps/21816/dl>

License usage (activated participant / of total): 0 / 4

Configured users: 1

Configured devices: 0

Active VPN connections: 0

Users: 0

Devices: 0

Logged on as "Rampage"

[Log off](#)

Licenses

▼ System

- Overview
- Logfile
- Network configuration
- Ping
- Static routes
- Date & time settings
- SMS & E-mail
- Licenses
- UMC settings
- Update
- Upload Server
- Backup & restore
- Syslog client
- Debug login

► Remote connections

► User accounts

► Security

► My account

<input type="checkbox"/>	License type	License number	Activation date	License value	Status	Actions
<input type="checkbox"/>	Demo License	00000-00000-00000-0000-000000	-	0 / 4	Active	

[Release license](#)

Online license activation:

[Activate license](#)

Offline license activation:

Step 1: [Export license container](#)

Contact Customer Support
- <https://support.industry.siemens.com>

Step 2: - E-Mail: support.automation@siemens.com
- Telephone: +49 911 865 722

For more information on this topic, refer to the online help.

*Select license container:

Step 3: [浏览...](#)[Import License Update](#)

SIEMENS

SINEMA Remote Connect

Help

6/9/2020 4:20:45 PM

Language: English

Logged on as "Rampage"

Log off

Exit dialog

New License

License number

Activation

* License number:

Next

可以备份和恢复 RC server 的配置

SIEMENS

SINEMA Remote Connect

Help

6/9/2020 4:21:29 PM

Language: English

Logged on as "Rampage"

Log off

System

Overview

Logfile

Network configuration

Ping

Static routes

Date & time settings

SMS & E-mail

Licenses

UMC settings

Update

Upload Server

Backup & restore

Syslog client

Debug login

Remote connections

User accounts

Security

My account

Backups & restore

Backup copies

Settings

* Maximum number of local backup copies:

20

* Automatic backup interval:

Disabled

* Automatic backup time (UTC):

23:00:00

* Coding key:

* Confirm coding key:

Specify the coding key before you make a backup. The backup copy will be encrypted with this coding key.

Save

可以通过 Remote connections 下的 Devices 创建远程站（S615 等支持 SINEMA RC 的路由设备）：

SIEMENS

SINEMA Remote Connect

Help

6/9/2020 4:24:53 PM

Language: English

Logged on as "Rampage"

Log off

System

Remote connections

Devices

Device update

Address spaces

Participant groups

Communication relations

User accounts

Security

My account

Devices

No filter active

Search filter: All

Precise match

Apply filter

Show all

	Device name	VPN address	Remote subnet	Virtual subnet	Status	Last connection	Location	Connection type	VPN protocol	Actions
<input type="checkbox"/>										

Create

可以通过 User accounts 下的 Users&Roles 创建登录 RC Client 的账户，并设置相关的规则：

SIEMENS

SINEMA Remote Connect

Help

6/9/2020 4:25:40 PM

Language: English

Logged on as "Rampage"

Log off

System

Remote connections

User accounts

Users & Roles

Security

My account

Users and roles

UserRolesUser agreement

No filter active

Search filter: All

Precise match

Apply filter

Show all

	User name	VPN address	First name	Last name	Account created	Date of the last login	Status	VPN protocol	Actions
<input type="checkbox"/>	Rampage	-	-	-	June 9, 2020, 11:34 p.m.	June 9, 2020, 4:16 p.m.	Offline	OpenVPN	

CreateCopyDelete

Number of users to display: 20