






Connector 连接器	Order No. 订货号	Description 描述	Image 图片	Incr. Encoder w/o Brkae 增量式无抱闸	Incr. Encoder with Brkae 增量式带抱闸	Abs. Encoder w/o Brkae 绝对值无抱闸	Abs. Encoder with Brkae 绝对值带抱闸
<b>V90 高惯量 (0.4 ~ 7.0 kw) 及低惯量 (1.5 ~ 2.0 kw)</b>							
Power Connector Motor side 电机动力插头	6FX2003-0LL11	POWER CONNECTOR 6FX2003-0LL11 FOR CONNECTION TO S-1FL6 HI 4-POLES INSULATOR, UNION NUT 4 X SOCKET CONTACT (1- 2.5 MM <sup>2</sup> ) D7.5 TO D12 MM CONTENT 30 PIECES		✓	✓	✓	✓
Brake Connector Motor side 电机抱闸插头	6FX2003-0LL51	BRAKE CONNECTOR 6FX2003-0LL51 FOR CONNECTION TO S-1FL6 HI 2-POLES INSULATOR, BAJONETT LOCK 2 X SOCKET CONTACT (0.5- 0.75 MM <sup>2</sup> ) D6 TO D8 MM CONTENT 30 PIECES			✓		✓
ABS. Signal Connector MotorSide 电机绝对值编码器插头	6FX2003-0DB11	ABS. SIGNAL CONNECTOR 6FX2003-0DB11 FOR CONNECTION TO S-1FL6 HI 8-POLES INSULATOR, BAJONETT LOCK 8 X SOCKET CONTACT (0.2- 0.25MM <sup>2</sup> ) D6 TO D8 MM CONTENT 30 PIECES				✓	✓
INCR. Signal Connector MotorSide 电机增量式编码器插头	6FX2003-0SL11	INCR. SIGNAL CONNECTOR 6FX2003-0SL11 FOR CONNECTION TO S-1FL6 HI 8-POLES INSULATOR, BAJONETT LOCK 8 X SOCKET CONTACT (0.2- 0.25 MM <sup>2</sup> ) D6 TO D8 MM CONTENT 30 PIECES		✓	✓		
Encoder Connector Drive Side 驱动器编码器插头	6FX2003-0SB14	SIGNAL CONNECTOR 6FX2003-0SB14 FOR CONNECT. TO SINAMICS V90 14-POLES INSULATOR, MDR BAJONETT LOCK 14 X PIN CONTACT (0.05-0.2 MM <sup>2</sup> ) D6 TO D8 MM CONTENT 30 PIECES		✓	✓	✓	✓
Control/setpoint signal cable Connector Drive side 驱动器控制信号插头	6SL3260-2NA00-0VA0	SETPOINT CONNECTOR FOR CONNECT.TO SINAMICS V90 WITH CONTROLLER 50-POLES INSULATOR, MDR 50X PIN CONTACTS (0.05-0.2 MM <sup>2</sup> ) CONTENT 30 PIECES		✓	✓	✓	✓

Connector 连接器	Order No. 订货号	Description 描述	Image 图片	Incr. Encoder w/o Brkæ 增量式无抱闸	Incr. Encoder with Brkæ 增量式带抱闸	Abs. Encoder w/o Brkæ 绝对值无抱闸	Abs. Encoder with Brkæ 绝对值带抱闸
<b>V90 低惯量 (0.1 ~ 1.0kw)</b>							
Power Connector Motor side 电机动力插头	6FX2003-0LL12	POWER CONNECTOR 6FX2003-0LL12 FOR CONNECTION TO S-1FL6 LI 4-POLES INSULATOR, 4 X SOCKET CONTACT(0.5-0.75MM <sup>2</sup> ) CONTENT 5 PIECE		✓	✓		
Brake Connector Motor side 电机抱闸插头	6FX2003-0LL52	POWER CONNECTOR 6FX2003-0LL12 FOR CONNECTION TO S-1FL6 LI 2-POLES INSULATOR, 2 X SOCKET CONTACT(0.5-0.75MM <sup>2</sup> ) CONTENT 5 PIECE			✓		
INCR. Signal Connector MotorSide 电机增量式编码器插头	6FX2003-0SL12	SIGNAL CONNECTOR 6FX2003-0SL12 FOR CONNECTION TO S-1FL6 LI 12-POLE INSULATOR 8 X SOCKET CONTACT(0.2-0.25MM <sup>2</sup> ) CONTENT 5 PIECE		✓	✓		
Encoder Connector Drive Side 驱动器编码器插头	6FX2003-0SB14	SIGNAL CONNECTOR 6FX2003-0SB14 FOR CONNECT. TO SINAMICS V90 14-POLES INSULATOR, MDR BAJONETT LOCK 14 X PIN CONTACT (0.05-0.2 MM <sup>2</sup> ) D6 TO D8 MM CONTENT 30 PIECES		✓	✓		
Control/setpoint signal cable Connector Drive side 驱动器控制信号插头	6SL3260-2NA00-0VA0	SETPOINT CONNECTOR FOR CONNECT. TO SINAMICS V90 WITH CONTROLLER 50-POLES INSULATOR, MDR 50X PIN CONTACTS (0.05-0.2 MM <sup>2</sup> ) CONTENT 30 PIECES		✓	✓		