


日期	时间	编号	消息文本	过程值： 1	过程值： 2
29/06/2017	15:38:31	1	升温到初温，温度77.0℃，压力0.05bar	77	0.0451637
29/06/2017	15:42:28	2	升温到杀菌温度，温度85.0℃，压力1.89bar	85	1.89443
29/06/2017	15:58:28	3	升温过冲缓冲，温度120.6℃，压力3.26bar	120.6	3.25911
29/06/2017	15:59:28	4	恒温预进入，温度122.1℃，压力3.26bar	122.1	3.26399
29/06/2017	15:59:58	5	恒温杀菌计时，温度122.1℃，压力3.26bar	122.1	3.25789
29/06/2017	16:15:58	6	冷却1开始，温度122.0℃，压力3.22bar	122	3.22371
29/06/2017	16:18:47	7	冷却2开始，温度85.1℃，压力1.93bar	85.1	1.92983
29/06/2017	16:32:01	8	冷却3开始，温度42.1℃，压力1.01bar	42.1	1.00825
29/06/2017	16:33:58	9	冷却4开始，温度40.4℃，压力0.32bar	40.4	0.318587
29/06/2017	16:34:58	10	排水，温度40.7℃，压力0.25bar，液位？	40.7	0.252672





日期/时间	温度	压力	釜底	F0
17-06-29 15:38:31	76.8	0.05		
17-06-29 15:38:41	77.4	0.17		
17-06-29 15:38:51	77.5	0.28		
17-06-29 15:39:01	77.1	0.31		
17-06-29 15:39:11	76.9	0.41		
17-06-29 15:39:21	76.8	0.47		
17-06-29 15:39:31	76.7	0.57		
17-06-29 15:39:41	76.8	0.65		
17-06-29 15:39:51	76.7	0.72		
17-06-29 15:40:01	76.8	0.77		
17-06-29 15:40:11	78.6	0.85		
17-06-29 15:40:21	79.4	0.92		
17-06-29 15:40:31	80.1	1.00		
17-06-29 15:40:41	80.6	1.06		
17-06-29 15:40:51	81.3	1.14		
17-06-29 15:41:01	81.1	1.22		
17-06-29 15:41:11	81.2	1.33		
17-06-29 15:41:21	81.8	1.41		
17-06-29 15:41:31	82.3	1.49		
17-06-29 15:41:41	82.7	1.52		
17-06-29 15:41:51	83.4	1.59		
17-06-29 15:42:01	83.5	1.67		
17-06-29 15:42:11	83.8	1.75		
17-06-29 15:42:21	84.3	1.82		
17-06-29 15:42:31	85.0	1.89		
17-06-29 15:42:41	85.3	1.96		
17-06-29 15:42:51	85.5	1.97		
17-06-29 15:43:01	86.1	1.99		
17-06-29 15:43:11	86.3	2.00		
17-06-29 15:43:21	86.5	2.01		

日期/时间	温度	压力	釜底	F0
17-06-29 15:43:31	87.5	2.02		
17-06-29 15:43:41	87.0	2.03		
17-06-29 15:43:51	88.0	2.05		
17-06-29 15:44:01	88.1	2.06		
17-06-29 15:44:11	88.6	2.07		
17-06-29 15:44:21	88.7	2.07		
17-06-29 15:44:31	89.0	2.09		
17-06-29 15:44:41	90.1	2.11		
17-06-29 15:44:51	90.0	2.11		
17-06-29 15:45:01	90.6	2.13		
17-06-29 15:45:11	90.6	2.13		
17-06-29 15:45:21	91.0	2.15		
17-06-29 15:45:31	91.7	2.17		
17-06-29 15:45:41	91.8	2.18		
17-06-29 15:45:51	92.3	2.19		
17-06-29 15:46:01	92.7	2.21		
17-06-29 15:46:11	92.8	2.22		
17-06-29 15:46:21	93.6	2.23		
17-06-29 15:46:31	94.0	2.25		
17-06-29 15:46:41	94.1	2.27		
17-06-29 15:46:51	94.8	2.28		
17-06-29 15:47:01	94.8	2.29		
17-06-29 15:47:11	95.6	2.31		
17-06-29 15:47:21	95.5	2.32		
17-06-29 15:47:31	96.0	2.34		
17-06-29 15:47:41	96.8	2.35		
17-06-29 15:47:51	96.6	2.36		
17-06-29 15:48:01	97.0	2.38		
17-06-29 15:48:11	97.5	2.40		
17-06-29 15:48:21	97.9	2.42		

日期/时间	温度	压力	釜底	F0
17-06-29 15:48:31	98.1	2.44		
17-06-29 15:48:41	98.9	2.47		
17-06-29 15:48:51	99.4	2.48		
17-06-29 15:49:01	99.4	2.49		
17-06-29 15:49:11	99.8	2.51		
17-06-29 15:49:21	100.2	2.52		
17-06-29 15:49:31	100.5	2.53		
17-06-29 15:49:41	100.9	2.55		
17-06-29 15:49:51	101.3	2.56		
17-06-29 15:50:01	101.3	2.57		
17-06-29 15:50:11	101.9	2.60		
17-06-29 15:50:21	102.3	2.61		
17-06-29 15:50:31	103.0	2.65		
17-06-29 15:50:41	103.4	2.66		
17-06-29 15:50:51	103.8	2.69		
17-06-29 15:51:01	104.1	2.70		
17-06-29 15:51:11	104.3	2.71		
17-06-29 15:51:21	104.5	2.73		
17-06-29 15:51:31	105.0	2.72		
17-06-29 15:51:41	105.4	2.74		
17-06-29 15:51:51	105.8	2.77		
17-06-29 15:52:01	106.2	2.77		
17-06-29 15:52:11	106.5	2.76		
17-06-29 15:52:21	106.9	2.78		
17-06-29 15:52:31	107.3	2.80		
17-06-29 15:52:41	107.8	2.83		
17-06-29 15:52:51	108.1	2.81		
17-06-29 15:53:01	108.4	2.83		
17-06-29 15:53:11	108.8	2.85		
17-06-29 15:53:21	109.2	2.87		

日期/时间	温度	压力	釜底	F0
17-06-29 15:53:31	109.5	2.86		
17-06-29 15:53:41	109.8	2.89		
17-06-29 15:53:51	110.4	2.91		
17-06-29 15:54:01	110.8	2.93		
17-06-29 15:54:11	111.1	2.92		
17-06-29 15:54:21	111.3	2.94		
17-06-29 15:54:31	111.9	2.97		
17-06-29 15:54:41	112.3	2.94		
17-06-29 15:54:51	112.5	2.97		
17-06-29 15:55:01	112.8	2.99		
17-06-29 15:55:11	113.3	3.02		
17-06-29 15:55:21	113.7	3.01		
17-06-29 15:55:31	114.0	3.03		
17-06-29 15:55:41	114.5	3.02		
17-06-29 15:55:51	115.0	3.06		
17-06-29 15:56:01	115.4	3.08		
17-06-29 15:56:11	115.5	3.06		
17-06-29 15:56:21	115.8	3.08		
17-06-29 15:56:31	116.2	3.11		
17-06-29 15:56:41	116.5	3.09		
17-06-29 15:56:51	117.1	3.13		
17-06-29 15:57:01	117.5	3.16		
17-06-29 15:57:11	117.7	3.15		
17-06-29 15:57:21	118.3	3.18		
17-06-29 15:57:31	118.5	3.17		
17-06-29 15:57:41	118.8	3.21		
17-06-29 15:57:51	119.5	3.20		
17-06-29 15:58:01	119.8	3.23		
17-06-29 15:58:11	120.2	3.21		
17-06-29 15:58:21	120.4	3.24		

日期/时间	温度	压力	釜底	F0
17-06-29 15:58:31	120.8	3.26		
17-06-29 15:58:41	121.1	3.26		
17-06-29 15:58:51	121.5	3.25		
17-06-29 15:59:01	121.6	3.24		
17-06-29 15:59:11	121.8	3.27		
17-06-29 15:59:21	121.9	3.26		
17-06-29 15:59:31	122.0	3.26		
17-06-29 15:59:41	122.1	3.23		
17-06-29 15:59:51	122.2	3.25		
17-06-29 16:00:01	122.2	3.26		
17-06-29 16:00:11	122.4	3.26		
17-06-29 16:00:21	122.3	3.27		
17-06-29 16:00:31	122.3	3.27		
17-06-29 16:00:41	122.3	3.27		
17-06-29 16:00:51	122.5	3.22		
17-06-29 16:01:01	122.3	3.24		
17-06-29 16:01:11	122.3	3.24		
17-06-29 16:01:21	122.3	3.24		
17-06-29 16:01:31	122.4	3.25		
17-06-29 16:01:41	122.4	3.24		
17-06-29 16:01:51	122.3	3.25		
17-06-29 16:02:01	122.3	3.25		
17-06-29 16:02:11	122.2	3.24		
17-06-29 16:02:21	122.2	3.24		
17-06-29 16:02:31	122.2	3.25		
17-06-29 16:02:41	122.2	3.24		
17-06-29 16:02:51	122.1	3.24		
17-06-29 16:03:01	122.1	3.24		
17-06-29 16:03:11	122.1	3.24		
17-06-29 16:03:21	122.1	3.23		

日期/时间	温度	压力	釜底	F0
17-06-29 16:03:31	122.1	3.24		
17-06-29 16:03:41	122.1	3.23		
17-06-29 16:03:51	122.1	3.23		
17-06-29 16:04:01	122.0	3.23		
17-06-29 16:04:11	122.0	3.23		
17-06-29 16:04:21	122.0	3.23		
17-06-29 16:04:31	122.0	3.23		
17-06-29 16:04:41	121.9	3.23		
17-06-29 16:04:51	121.9	3.23		
17-06-29 16:05:01	121.9	3.22		
17-06-29 16:05:11	121.9	3.23		
17-06-29 16:05:21	121.9	3.22		
17-06-29 16:05:31	121.8	3.22		
17-06-29 16:05:41	121.8	3.22		
17-06-29 16:05:51	121.8	3.22		
17-06-29 16:06:01	121.8	3.22		
17-06-29 16:06:11	121.8	3.22		
17-06-29 16:06:21	121.8	3.22		
17-06-29 16:06:31	121.8	3.22		
17-06-29 16:06:41	121.8	3.21		
17-06-29 16:06:51	121.8	3.22		
17-06-29 16:07:01	121.8	3.21		
17-06-29 16:07:11	121.8	3.21		
17-06-29 16:07:21	121.8	3.22		
17-06-29 16:07:31	121.8	3.22		
17-06-29 16:07:41	121.8	3.21		
17-06-29 16:07:51	121.8	3.22		
17-06-29 16:08:01	121.9	3.22		
17-06-29 16:08:11	121.9	3.22		
17-06-29 16:08:21	121.9	3.22		

日期/时间	温度	压力	釜底	F0
17-06-29 16:08:31	121.9	3.23		
17-06-29 16:08:41	122.0	3.23		
17-06-29 16:08:51	122.0	3.22		
17-06-29 16:09:01	122.0	3.23		
17-06-29 16:09:11	122.0	3.23		
17-06-29 16:09:21	122.1	3.23		
17-06-29 16:09:31	122.1	3.23		
17-06-29 16:09:41	122.1	3.23		
17-06-29 16:09:51	122.1	3.23		
17-06-29 16:10:01	122.1	3.23		
17-06-29 16:10:11	122.1	3.23		
17-06-29 16:10:21	122.1	3.24		
17-06-29 16:10:31	122.1	3.24		
17-06-29 16:10:41	122.1	3.24		
17-06-29 16:10:51	122.1	3.24		
17-06-29 16:11:01	122.1	3.24		
17-06-29 16:11:11	122.1	3.24		
17-06-29 16:11:21	122.1	3.24		
17-06-29 16:11:31	122.1	3.24		
17-06-29 16:11:41	122.2	3.24		
17-06-29 16:11:51	122.2	3.24		
17-06-29 16:12:01	122.2	3.25		
17-06-29 16:12:11	122.1	3.24		
17-06-29 16:12:21	122.1	3.25		
17-06-29 16:12:31	122.1	3.24		
17-06-29 16:12:41	122.1	3.24		
17-06-29 16:12:51	122.1	3.24		
17-06-29 16:13:01	122.1	3.24		
17-06-29 16:13:11	122.1	3.24		
17-06-29 16:13:21	122.1	3.24		

日期/时间	温度	压力	釜底	F0
17-06-29 16:13:31	122.1	3.24		
17-06-29 16:13:41	122.1	3.24		
17-06-29 16:13:51	122.1	3.23		
17-06-29 16:14:01	122.1	3.24		
17-06-29 16:14:11	122.1	3.23		
17-06-29 16:14:21	122.1	3.24		
17-06-29 16:14:31	122.1	3.23		
17-06-29 16:14:41	122.1	3.24		
17-06-29 16:14:51	122.1	3.23		
17-06-29 16:15:01	122.1	3.23		
17-06-29 16:15:11	122.0	3.23		
17-06-29 16:15:21	122.0	3.23		
17-06-29 16:15:31	122.0	3.23		
17-06-29 16:15:41	122.0	3.23		
17-06-29 16:15:51	122.0	3.23		
17-06-29 16:16:01	122.0	3.23		
17-06-29 16:16:11	121.5	3.20		
17-06-29 16:16:21	121.3	3.09		
17-06-29 16:16:31	117.8	2.98		
17-06-29 16:16:41	115.7	2.86		
17-06-29 16:16:51	111.5	2.71		
17-06-29 16:17:01	108.1	2.61		
17-06-29 16:17:11	105.4	2.53		
17-06-29 16:17:21	103.7	2.42		
17-06-29 16:17:31	101.7	2.32		
17-06-29 16:17:41	99.0	2.21		
17-06-29 16:17:51	96.5	2.11		
17-06-29 16:18:01	95.0	2.02		
17-06-29 16:18:11	92.1	1.94		
17-06-29 16:18:21	90.8	1.94		

日期/时间	温度	压力	釜底	F0
17-06-29 16:18:31	88.1	1.94		
17-06-29 16:18:41	86.0	1.92		
17-06-29 16:18:51	84.8	1.95		
17-06-29 16:19:01	82.8	1.95		
17-06-29 16:19:11	82.0	1.91		
17-06-29 16:19:21	81.1	1.91		
17-06-29 16:19:31	81.4	1.91		
17-06-29 16:19:41	81.4	1.90		
17-06-29 16:19:51	81.4	1.90		
17-06-29 16:20:01	81.3	1.89		
17-06-29 16:20:11	81.0	1.89		
17-06-29 16:20:21	80.6	1.87		
17-06-29 16:20:31	80.1	1.86		
17-06-29 16:20:41	79.5	1.85		
17-06-29 16:20:51	78.6	1.83		
17-06-29 16:21:01	77.8	1.81		
17-06-29 16:21:11	77.3	1.80		
17-06-29 16:21:21	76.8	1.78		
17-06-29 16:21:31	76.0	1.78		
17-06-29 16:21:41	75.6	1.76		
17-06-29 16:21:51	75.1	1.75		
17-06-29 16:22:01	74.6	1.73		
17-06-29 16:22:11	74.1	1.71		
17-06-29 16:22:21	73.3	1.70		
17-06-29 16:22:31	72.8	1.69		
17-06-29 16:22:41	72.3	1.68		
17-06-29 16:22:51	71.6	1.67		
17-06-29 16:23:01	71.3	1.66		
17-06-29 16:23:11	70.5	1.65		
17-06-29 16:23:21	70.2	1.63		

日期/时间	温度	压力	釜底	F0
17-06-29 16:23:31	69.7	1.63		
17-06-29 16:23:41	69.0	1.61		
17-06-29 16:23:51	68.5	1.60		
17-06-29 16:24:01	67.9	1.60		
17-06-29 16:24:11	67.5	1.58		
17-06-29 16:24:21	67.1	1.57		
17-06-29 16:24:31	66.4	1.56		
17-06-29 16:24:41	65.5	1.55		
17-06-29 16:24:51	65.3	1.54		
17-06-29 16:25:01	64.7	1.52		
17-06-29 16:25:11	64.0	1.52		
17-06-29 16:25:21	63.6	1.51		
17-06-29 16:25:31	63.0	1.50		
17-06-29 16:25:41	62.5	1.50		
17-06-29 16:25:51	62.0	1.48		
17-06-29 16:26:01	61.3	1.48		
17-06-29 16:26:11	60.6	1.46		
17-06-29 16:26:21	60.3	1.46		
17-06-29 16:26:31	59.8	1.45		
17-06-29 16:26:41	59.2	1.44		
17-06-29 16:26:51	58.5	1.43		
17-06-29 16:27:01	58.0	1.41		
17-06-29 16:27:11	57.5	1.41		
17-06-29 16:27:21	56.8	1.40		
17-06-29 16:27:31	56.4	1.40		
17-06-29 16:27:41	55.8	1.38		
17-06-29 16:27:51	55.2	1.37		
17-06-29 16:28:01	54.6	1.34		
17-06-29 16:28:11	54.3	1.33		
17-06-29 16:28:21	53.7	1.33		

日期/时间	温度	压力	釜底	F0
17-06-29 16:28:31	53.1	1.32		
17-06-29 16:28:41	52.5	1.32		
17-06-29 16:28:51	52.1	1.27		
17-06-29 16:29:01	51.5	1.26		
17-06-29 16:29:11	50.9	1.25		
17-06-29 16:29:21	50.4	1.25		
17-06-29 16:29:31	49.9	1.25		
17-06-29 16:29:41	49.2	1.24		
17-06-29 16:29:51	48.6	1.20		
17-06-29 16:30:01	48.0	1.20		
17-06-29 16:30:11	47.6	1.18		
17-06-29 16:30:21	47.1	1.18		
17-06-29 16:30:31	46.5	1.14		
17-06-29 16:30:41	46.1	1.14		
17-06-29 16:30:51	45.4	1.14		
17-06-29 16:31:01	45.1	1.13		
17-06-29 16:31:11	44.5	1.10		
17-06-29 16:31:21	44.0	1.09		
17-06-29 16:31:31	43.6	1.09		
17-06-29 16:31:41	43.1	1.08		
17-06-29 16:31:51	42.7	1.05		
17-06-29 16:32:01	42.1	1.01		
17-06-29 16:32:11	41.8	1.01		
17-06-29 16:32:21	41.2	0.96		
17-06-29 16:32:31	40.9	0.88		
17-06-29 16:32:41	40.8	0.81		
17-06-29 16:32:51	40.3	0.74		
17-06-29 16:33:01	40.3	0.68		
17-06-29 16:33:11	40.3	0.62		
17-06-29 16:33:21	40.1	0.55		

日期/时间	温度	压力	釜底	F0
17-06-29 16:33:31	40.2	0.49		
17-06-29 16:33:41	40.3	0.42		
17-06-29 16:33:51	40.3	0.36		
17-06-29 16:34:01	40.3	0.30		
17-06-29 16:34:11	40.3	0.25		
17-06-29 16:34:21	40.5	0.25		
17-06-29 16:34:31	40.5	0.26		
17-06-29 16:34:41	40.6	0.26		
17-06-29 16:34:51	40.5	0.25		
17-06-29 16:35:01	40.7	0.26		
17-06-29 16:35:11	40.4	0.26		
17-06-29 16:35:21	40.0	0.23		
17-06-29 16:35:31	40.3	0.24		
17-06-29 16:35:41	40.2	0.22		
17-06-29 16:35:51	40.3	0.21		
17-06-29 16:36:01	40.4	0.20		
17-06-29 16:36:11	40.5	0.19		
17-06-29 16:36:21	40.5	0.17		
17-06-29 16:36:31	40.5	0.17		
17-06-29 16:36:41	40.5	0.15		
17-06-29 16:36:51	40.6	0.14		
17-06-29 16:37:01	40.6	0.14		
17-06-29 16:37:11	40.7	0.13		
17-06-29 16:37:21	40.8	0.12		
17-06-29 16:37:31	40.8	0.09		
17-06-29 16:37:41	40.8	0.10		
17-06-29 16:37:51	40.8	0.10		