

## SGRJ\_V14\_V15 / PLC\_1 [CPU 1516-3 PN/DP] / Program blocks

### FC914SELECTED\_4 [FC914]

#### FC914SELECTED\_4 Properties

##### General

<b>Name</b>	FC914SELECTED_4	<b>Number</b>	914	<b>Type</b>	FC	<b>Language</b>	S
<b>Numbering</b>	Manual						

##### Information

<b>Title</b>		<b>Author</b>	ABLYY	<b>Comment</b>		<b>Family</b>	A
<b>Version</b>	1.0	<b>User-defined ID</b>					

#### FC914SELECTED\_4

Name	Data type	Offset	Default value	Comment
▼ Input				
IN1	Bool			
IN2	Bool			
IN3	Bool			
IN4	Bool			
NUMBER1	Real			
NUMBER2	Real			
NUMBER3	Real			
NUMBER4	Real			
Output				
▼ InOut				
OUTPUT	Real			
Temp				
Constant				
▼ Return				
FC914SELECTED_4	Void			

#### Network 1

Totally Integrated  
Automation Portal

```
0001      A      #IN1
0002      JNB    _001
0003      L      #NUMBER1
0004      T      #OUTPUT
0005  _001: NOP 0
```

**Network 2:**

```
0001      A      #IN2
0002      JNB    _002
0003      L      #NUMBER2
0004      T      #OUTPUT
0005  _002: NOP 0
```

**Network 3:**

```
0001      A      #IN3
0002      JNB    _003
0003      L      #NUMBER3
0004      T      #OUTPUT
0005  _003: NOP 0
```

**Network 4:**

```
0001      A      #IN4
0002      JNB    _005
0003      L      #NUMBER4
0004      T      #OUTPUT
0005  _005: NOP 0
```

**Network 5:**

```
0003      AN      #IN3
0004      AN      #IN4
0005      JNB     _006
0006      L       0.0
0007      T       #OUTPUT
0008  _006: NOP 0
```

### Network 6:

```
0001
0002      SET
0003      SAVE
0004      CLR
0005      BE
```